

## ION-EXCHANGE COLUMNS

### IEC D / d / L

Designed to be filled with ion-exchange resins or filtering materials.

Preliminary preparation of the analyzed water sample, including H-cation exchange, high purity water getting, mechanical filtration.

- Optimum output 30 dm<sup>3</sup>/h.
- Air deflation valves.
- Stainless filters.



**TABLE OF THE COLUMN VERSION'S DIMENSIONS**

D	20	30	40	50	60	70
d	16	24	32	44	50	62
L	from 190 to 950					

D/d/L – outer / inner diameter / length, mm

The company reserves the right to make changes into the products configuration without their performance degradation

